



## C25DNF330B Open N-R 3P 30A DP Cont Box Lugs W/QC Term 240vac

*Eaton Corp*

Catalog Number	C25DNF330B
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 30A, 110V/50 HZ, 120V/60 HZ, Open With Metal Mounting Plate, 15-50A, Two- or 3P, 15-50A, Two- and 3P, Contactor, 3P, Global Ratings, Box Lugs (Posidrive Setscrew) and Quick Connect Terminals
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

Coil Voltage	440-480 Vac, 50/60 Hz
Enclosure Type	Open with metal mounting plate

### Dimensions and Weight

Depth	3.35
Height	3.75
Width	2.4

### Descriptions

Description	OPEN N-R 3P 30A DP CONT BOX LUGS W/QC TERM 240VAC
extra long description	ETN C25DNF330B OP N-R 3P 30ADPCNT B
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 30A, 110V/50 Hz, 120V/60 Hz, Open with metal mounting plate, 15-50A, two- or 3P, 15-50A, two- and 3P, Contactor, 3P, Global ratings, Box lugs (posidrive setscrew) and quick connect terminals
Product Type	Op N-R 3P 30ADPCNT BXLGS W/Qc240ac

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116311347
Manufacturers Part Number	C25DNF330B
UPC	782116311347

### Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

### Packaging

Carton	1
Weight Per each	1.19



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /  
Institutional Buildings / Structures - OtherElec Assemblies, Panels  
& EOEM - Electrical Assemblies, Panels and EOEMs

standard

UL Recognized, CSA Certified, UL Listed file E1491 (Guide Number  
NLDX2), RoHS Compliant