



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25DNF340A Open N-R 3P 40A DP Cont Box Lugs W/QC Term 120vac *Eaton Corp*

Catalog Number	C25DNF340A
Manufacturer	Eaton Corp
Description	Definite Purpose Control - Contactor, 3 Poles, 40 A, 110 to 120 V Ac, 40 A Resistive Load, 1/3 Phases, 7-1/2 HP (Single Phase);10 HP (Three Phase);5.5 KW (Single Phase);7.5 KW (Three Phase) Motor Power, 15 to 50 A Frame, Quick Connect Terminal Connection, -13 °F Operating Temperature, +158 °F Operating Temperature, Din Rail Mount, 50 to 60 HZ, 3.75 In Overall Height, 3.35 In Overall Length, 2.40 In Overall Width, 1.19 LB
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

Features

Enclosure Type	Open with metal mounting plate
induct amp/res amp rating	40/50
Voltage Rating	120

Dimensions and Weight

Depth	3.35
Height	3.75
Width	2.4

Descriptions

Description	OPEN N-R 3P 40A DP CONT BOX LUGS W/QC TERM 120VAC
extra long description	ETN C25DNF340A OP N-R 3P 40ADPCNT B

Manufacturer Information

Brand	Eaton
GTIN	00782116300662
UPC	782116300662

Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

Packaging

Carton	1
Package	20
Weight Per each	1.19

Uses, Certifications, and Standards

standard	UL Recognized,CSA Certified,RoHS Compliant
----------	--