



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C25DNF340T Open N-R 3P 40A DP Cont Box Lugs W/QC Term 24VAC C *Eaton Corp*

Catalog Number	C25DNF340T
Manufacturer	Eaton Corp
Description	Definite Purpose Control - Contactor, 3 Poles, 40 A, 24 V Ac, 40 A Resistive Load, 1/3 Phases, 7-1/2 HP (Single Phase);10 HP (Three Phase);5.5 KW (Single Phase);7.5 KW (Three Phase) Motor Power, 15 to 50 A Frame, Quick Connect Terminal Connection, -13 °F Operating Temperature, +158 °F Operating Temperature, Din Rail Mount, 50 to 60 HZ, 3.75 In Overall Height, 3.35 In Overall Length, 2.40 In Overall Width, 1.05 LB
Weight per unit	1.1 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

connection	Quick
dimensions	3.3500 IN X 2.4000 IN X 2.3000 IN
Enclosure Type	Open with metal mounting plate

### Descriptions

Description	OPEN N-R 3P 40A DP CONT BOX LUGS W/QC TERM 24VAC C
extra long description	ETN C25DNF340T OP N-R 3P 40ADPCNT B

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116300709
UPC	782116300709

### Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

### Packaging

Carton	1
Weight Per each	1.05

### Uses, Certifications, and Standards

standard	CSA Certified,UL Recognized,RoHS Compliant
----------	--