



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C502H 2 HR Twist Timer With Metal Wallplate

Nsi Industries

Catalog Number	C502H
Manufacturer	Nsi Industries
Description	Twist Timer, 2 H Time Setting Mode, SPDT Contact Form, 2 H Time Setting, 125 to 277 V, 1 Pole, White, +32 °F Operating Temperature, +122 °F Operating Temperature, 3 X 5 In Size, 0.4 LB
Weight per unit	0.4000 (lbs/each)
Product Category	Electromechanical Time Switches

Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	2 Hour

Descriptions

Description	2 HR TWIST TIMER WITH METAL WALLPLATE
extra long description	TORK C502H Interval Timer 15 Min Me

Manufacturer Information

GTIN	00786261155078
Manufacturers Part Number	C502H
UPC	786261155078

Taxonomies, Classifications, and Categories

Category Description	1PH MANUAL STARTERS
Type	Spring Wound In Wall Time Switch-Commercial Grade

Packaging

Carton	1
Weight Per each	0.4

Uses, Certifications, and Standards

Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F
standard	cULus