



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C502H 2 HR Twist Timer With Metal Wallplate

Nsi Industries

| | |
|------------------|--|
| Catalog Number | C502H |
| Manufacturer | Nsi Industries |
| Description | Twist Timer, 2 H Time Setting Mode, SPDT Contact Form, 2 H Time Setting, 125 to 277 V, 1 Pole, White, +32 °F Operating Temperature, +122 °F Operating Temperature, 3 X 5 In Size, 0.4 LB |
| Weight per unit | 0.4000 (lbs/each) |
| Product Category | Electromechanical Time Switches |

Features

| | |
|----------------|-----------------|
| action | SPDT |
| Base | Wall Plate |
| Contact Rating | 125-250-277 VAC |
| Phase | Single Phase |
| Poles | 1 |
| Timing Range | 2 Hour |

Descriptions

| | |
|------------------------|---------------------------------------|
| Description | 2 HR TWIST TIMER WITH METAL WALLPLATE |
| extra long description | TORK C502H Interval Timer 15 Min Me |

Manufacturer Information

| | |
|---------------------------|----------------|
| GTIN | 00786261155078 |
| Manufacturers Part Number | C502H |
| UPC | 786261155078 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | 1PH MANUAL STARTERS |
| Type | Spring Wound In Wall Time Switch-Commercial Grade |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.4 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------------|
| Enclosure | Single Gang Wall Plate |
| environmental conditions | 32-122 F |
| Frequency Rating | 50-60 Hz |
| Mounting | Single Gang Wall Plate |
| Operating Temperature | 32-122 F |
| standard | cULus |