



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C6 #6 Cu Long Barrel Compression Butt Splice

Nsi Industries

Catalog Number	C6
Manufacturer	Nsi Industries
Description	Compression Splice Connector, #8 Awg Conductor Size, #6 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Blue Insulation Color, 2 Conductors, +90 °C Operating Temperature, 1.752 In Overall Length, Compression Terminal, 600 V, 0.04 LB/Ea
Weight per unit	0.0400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Blue
Finish	Tin Plated

Dimensions and Weight

Size	L=1.75 - OD=.300 - ID=.200
------	----------------------------

Descriptions

Description	#6 CU LONG BARREL COMPRESSION BUTT SPLICE
extra long description	NSI C-6 Easy Twist Closed End Conn
Features	Long Barrel TinnedCopperSplice6 AWG Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.

Manufacturer Information

GTIN	00662381037503
UPC	662381037503

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - CU Splice



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	100
Weight Per each	0.04

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)
Temperature Rating	90 C