

# Specifications

## Eaton CCP3023BC



Eaton Crouse-Hinds series PowerMate CCP plug, 30A, 0.390-1.375", Two-wire, three-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series PowerMate CCP plug
<b>CATALOG NUMBER</b>	CCP3023BC
<b>UPC</b>	662276276536
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	2.31 in
<b>PRODUCT WIDTH</b>	2.31 in
<b>PRODUCT WEIGHT</b>	2.2 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4X

### Product specifications

<b>AMPERAGE RATING</b>	30A
<b>GROUNDING TYPE</b>	Style 2
<b>CONFIGURATION</b>	Two-wire, three-pole
<b>CABLE DIAMETER</b>	0.390-1.375"

---

**VOLTAGE RATING**

600 Vac/250 Vdc

---

**MATERIAL**Copper-free aluminum

---

## Resources

**3D CAD DRAWING PACKAGE**[Eaton Crouse-Hinds CCP3023BC 3D drawing](#)**BROCHURES**[PowerMate Drilling Pin and Sleeve Devices brochure](#)**CATALOGS**[PowerMate Drilling Pin and Sleeve Devices catalog page](#)**CERTIFICATION REPORTS**[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)**INSTALLATION INSTRUCTIONS**[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)**SPECIFICATIONS AND DATASHEETS**[Eaton Specification Sheet - CCP3023BC](#)[PowerMate Connectors](#)

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications

## Eaton CCP3023BC



Eaton Crouse-Hinds series PowerMate CCP plug, 30A, 0.390-1.375", Two-wire, three-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series PowerMate CCP plug
<b>CATALOG NUMBER</b>	CCP3023BC
<b>UPC</b>	662276276536
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	2.31 in
<b>PRODUCT WIDTH</b>	2.31 in
<b>PRODUCT WEIGHT</b>	2.2 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4X

### Product specifications

<b>AMPERAGE RATING</b>	30A
<b>GROUNDING TYPE</b>	Style 2
<b>CONFIGURATION</b>	Two-wire, three-pole
<b>CABLE DIAMETER</b>	0.390-1.375"

---

**VOLTAGE RATING**

600 Vac/250 Vdc

---

**MATERIAL**Copper-free aluminum

---

## Resources

**3D CAD DRAWING PACKAGE**[Eaton Crouse-Hinds CCP3023BC 3D drawing](#)**BROCHURES**[PowerMate Drilling Pin and Sleeve Devices brochure](#)**CATALOGS**[PowerMate Drilling Pin and Sleeve Devices catalog page](#)**CERTIFICATION REPORTS**[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)**INSTALLATION INSTRUCTIONS**[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)**SPECIFICATIONS AND DATASHEETS**[Eaton Specification Sheet - CCP3023BC](#)[PowerMate Connectors](#)

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

