

Eaton CDR1023

Catalog Number: CDR1023

Eaton Crouse-Hinds series PowerMate CDR receptacle, 100A, Two-wire, three-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc



General specifications

| Product Name | Catalog Number |
|--|----------------|
| Eaton Crouse-Hinds series PowerMate CDR receptacle | CDR1023 |
| | UPC |
| | 662276277083 |
| Product Length/Depth | Product Height |
| 5.25 in | 4.25 in |
| Product Width | Product Weight |
| 4.25 in | 2.2 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Product specifications

Amperage Rating

100A

Grounding type

Style 2

Configuration

Two-wire, three-pole

Voltage rating

600 Vac/250 Vdc

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds CDR1023 3D drawing](#)

Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Receptacles\)](#)

Installation instructions

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)
[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

Specifications and datasheets

[Eaton Specification Sheet - CDR1023](#)
[PowerMate Connectors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)