





SECTION B-B





SECTION A-A

| | | | | | | | | | |
|-------------------------|--|--|--|---------------------------|--|--|--|---|--|
| NOTES | | | | 1. 35, 44, 65, 12 | | ALL DIMENSIONS ARE INCHES (MILLIMETERS) UNLESS SPECIFIED | | TOLERANCES xx ± 0.03(0.79) xxx ± 0.010 (0.25) | |
| MATERIAL | | | | COLOR GLASSER GRAY BR1813 | | DR. BY | | DATE | |
| FR POLYESTER FIBERGLASS | | | | | | 10/29/2007 | | | |
| REVISION RECORD | | | | DATE | | BY | | CHK BY | |
| DATE | | | | BY | | CHK BY | | DATE | |
| APD. BY | | | | DATE | | CUSTOMER | | BELDING, MICHIGAN 48809 | |
| SCALE | | | | DO NOT SCALE | | PART NAME | | PART NO. | |
| | | | | | | | | CF332 | |

THIS DRAWING AND THE INFORMATION HEREON ARE OUR PROPERTY AND MAY BE USED BY OTHERS ONLY AS AUTHORIZED BY STAN ENCLLOSURES DIVISION OF BELDING. RESISTANCE ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.



SECTION B-B



SECTION A-A

| | | | | | | | |
|--------------------------|--|-------------------------|--|--|--|---|--|
| NOTES | | 1. 35. 44. 66. 12 | | ALL DIMENSIONS ARE INCHES (MILLIMETERS) UNLESS SPECIFIED | | TOLERANCES xx ± 0.03(0.79) xxx ± 0.010 (0.25) | |
| MATERIAL | | FR POLYESTER FIBERGLASS | | DR. BY | | DATE | |
| COLOR GLAZER GRAY RR1813 | | | | 10/29/2007 | | | |
| REVISION RECORD | | DATE | | BY | | CHK. BY | |
| DATE | | BY | | CHK. BY | | DATE | |
| APD. BY | | DATE | | CUSTOMER | | BELDING, MICHIGAN 48809 | |
| SCALE | | DO NOT SCALE | | PART NAME | | PART NO. | |
| | | | | | | CF332 | |

THIS DRAWING AND THE INFORMATION HEREON ARE OUR PROPERTY AND MAY BE USED BY OTHERS ONLY AS AUTHORIZED BY STI. BELDING, DIVISION OF BELDING INDUSTRIES. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.