



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH10GEN5050SN Nema 1, 12 Circuit, 50A Manual Transfer Switch Wit Eaton Corp

Catalog Number	CH10GEN5050SN
Manufacturer	Eaton Corp
Description	Eaton CH Transfer Switch Panel, Switched Neutral Manual Transfer Switch, 50A Main, 50A Emergency, 10 Circuits, Nema 1 Enclosure, 12 KW, (6) Single-Pole 15A, (2) Single-Pole 20A, (1) Two-Pole 30A Feeder Breakers, Standard T Phasing
Weight per unit	24.0 (lbs/each)
Product Category	Fusible Special Application Sa

Features

media	Yes
-------	-----

Dimensions and Weight

Depth	16.8
Height	14.3
Width	4.4

Descriptions

Description	NEMA 1, 12 CIRCUIT, 50A MANUAL TRANSFER SWITCH WIT
extra long description	ETN CH10GEN5050SN Nema 1, 12 CKT, 5
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH transfer switch panel, Switched neutral manual transfer switch, 50A main, 50A emergency, 10 circuits, NEMA 1 enclosure, 12 kW, (6) single-pole 15A, (2) single-pole 20A, (1) two-pole 30A feeder breakers, Standard T phasing
Product Type	Nema 1, 12 CKT, 50A Man Transf Switch

Manufacturer Information

Brand	Eaton
GTIN	00786685268378
Manufacturers Part Number	CH10GEN5050SN
UPC	786685268378

Taxonomies, Classifications, and Categories

Category Description	TRANSFER SWITCHES
Type	Transfer switch panel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	24

Uses, Certifications, and Standards

Application	Other
standard	UL 1008,UL 67