

Eaton CH12L125R

Catalog Number: CH12L125R

Eaton CH main lug loadcenters, Cover included, Main lug only, 125A, B, Copper, NEMA 3R, Metallic, Overhead, CH, 12, 12, Three-wire, Single-phase, 120/240 V, #6-2/0 AWG



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CH12L125R
UPC	Product Length/Depth
782113097381	16.75 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
15.8 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

Product specifications

Special features

Cover included

Type

Main lug only

Amperage Rating

125 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

12

Number of spaces

12

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#6-2/0 AWG

Box size

B

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Catalogs

Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH12L125R

Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)