

Specifications



Photo is representative

Eaton CH16L200R

Eaton CH main lug loadcenters, Cover included, Main lug only, 200A, D, Copper, NEMA 3R, Metallic, Overhead, CH, 16, 16, Three-wire, Single-phase, 120/240 V, #4 AWG-300 kcmil

General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CH16L200R
UPC	782113097503
PRODUCT LENGTH/DEPTH	16.75 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15.8 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Rainproof panels are furnished with hub closure plates. Suitable for use as a service equipment when a circuit breaker is used as a main breaker. The main breaker is backfed and requires hold-down bracket kit catalog number ch125rb.



Product specifications

SPECIAL FEATURES Cover included

Resources

TYPE	Main lug only
AMPERAGE RATING	200 A
BUS MATERIAL	Copper
FEED TYPE	Overhead
MAIN CIRCUIT BREAKER	CH
NUMBER OF CIRCUITS	16
NUMBER OF SPACES	16
PHASE	Single-phase
VOLTAGE RATING	120/240 V
WIRE SIZE	#4 AWG-300 kcmil
BOX SIZE	D
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
NUMBER OF WIRES	3

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
MULTIMEDIA	AFCI Educational Video
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CH16L200R
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

