

Eaton CH18B100R

Catalog Number: CH18B100R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 100 A, C, Copper, NEMA 3R, Metallic, 10 kAIC, CH, 18, 18, Three-wire, Single-phase, #6-1/0 AWG, Overhead, 120/240 V

General specifications



Product Name	Catalog Number
Eaton CH main breaker loadcenter	CH18B100R
UPC	Product Length/Depth
782113097558	21 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
15.25 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Furnished with tub hub closure plates for rainproof hubs, refer to page 3-22. Loadcenter contains single insulated/bondable neutral.

Product specifications

Special features

Cover included

Type

Main breaker

Amperage Rating

100 A

Bus material

Copper

Main circuit breaker

CH

Number of circuits

18

Number of spaces

18

Phase

Single-phase

Wire size

#6-1/0 AWG

Feed type

Overhead

Voltage rating

120/240 V

Box size

C

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH18B100R](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CH18B100R

Catalog Number: CH18B100R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 100 A, C, Copper, NEMA 3R, Metallic, 10 kAIC, CH, 18, 18, Three-wire, Single-phase, #6-1/0 AWG, Overhead, 120/240 V

General specifications



Product Name

Eaton CH main breaker loadcenter

Catalog Number

CH18B100R

UPC

782113097558

Product Length/Depth

21 in

Product Height

5.19 in

Product Width

14.31 in

Product Weight

15.25 lb

Warranty

Limited lifetime

Certifications

UL 67

UL 50

Catalog Notes

Furnished with tub hub closure plates for rainproof hubs, refer to page 3-22.

Loadcenter contains single insulated/bondable neutral.



Powering Business Worldwide

Product specifications

Special features

Cover included

Type

Main breaker

Amperage Rating

100 A

Bus material

Copper

Main circuit breaker

CH

Number of circuits

18

Number of spaces

18

Phase

Single-phase

Wire size

#6-1/0 AWG

Feed type

Overhead

Voltage rating

120/240 V

Box size

C

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH18B100R](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)