

Specifications

Photo is representative



Eaton CH20L125R

Eaton CH main lug loadcenters, Cover included, Main lug only, 125A, C, Copper, NEMA 3R, Metallic, Overhead, CH, 20, 20, Three-wire, Single-phase, 120/240 V, #6-2/0 AWG

General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CH20L125R
UPC	782113097602
PRODUCT LENGTH/DEPTH	21 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	16 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

Product specifications

SPECIAL FEATURES
TYPE
AMPERAGE RATING
BUS MATERIAL
FEED TYPE
MAIN CIRCUIT BREAKER
NUMBER OF CIRCUITS
NUMBER OF SPACES
PHASE
VOLTAGE RATING
WIRE SIZE
BOX SIZE
ENCLOSURE
ENCLOSURE MATERIAL
NUMBER OF WIRES

EATON

Powering Business Worldwide

Specifications

Photo is representative



Eaton CH20L125R

Eaton CH main lug loadcenters, Cover included, Main lug only, 125A, C, Copper, NEMA 3R, Metallic, Overhead, CH, 20, 20, Three-wire, Single-phase, 120/240 V, #6-2/0 AWG

General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CH20L125R
UPC	782113097602
PRODUCT LENGTH/DEPTH	21 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	16 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

Product specifications

SPECIAL FEATURES
TYPE
AMPERAGE RATING
BUS MATERIAL
FEED TYPE
MAIN CIRCUIT BREAKER
NUMBER OF CIRCUITS
NUMBER OF SPACES
PHASE
VOLTAGE RATING
WIRE SIZE
BOX SIZE
ENCLOSURE
ENCLOSURE MATERIAL
NUMBER OF WIRES

EATON

Powering Business Worldwide