



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch loadcenter

CH22N125R

UPC:782113098524

Dimensions:

- **Height:** 5.19 IN
- **Length:** 21 IN
- **Width:** 14.31 IN

Notes:Furnished with hub closure plates.

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Cover included
- **Amperage Rating:** 125A
- **Box Size:** C
- **Bus Material:** Copper
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Feed Type:** Overhead
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 22
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #10-1/0 AWG

Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CH CONVERTIBLE, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eaton Specification Sheet - CH22N125R](#)



Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch loadcenter

CH22N125R

UPC:782113098524

Dimensions:

- **Height:** 5.19 IN
- **Length:** 21 IN
- **Width:** 14.31 IN

Notes:Furnished with hub closure plates.

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Cover included
- **Amperage Rating:** 125A
- **Box Size:** C
- **Bus Material:** Copper
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Feed Type:** Overhead
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 22
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #10-1/0 AWG

Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CH CONVERTIBLE, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eaton Specification Sheet - CH22N125R](#)



Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.