

# Eaton CH24B150R

Catalog Number: CH24B150R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 150 A, E, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 24, 24, Three-wire, Single-phase, #2/0 AWG-300 kcmil, Overhead, 120/240 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main breaker loadcenter	CH24B150R
<b>UPC</b>	<b>Product Length/Depth</b>
782113097763	29.13 in
<b>Product Height</b>	<b>Product Width</b>
5.19 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
32.85 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67 UL 50	Furnished with tub hub closure plates for rainproof hubs, refer to page 3-22. Loadcenter contains single insulated/bondable neutral.

## Product specifications

### Special features

Cover included

### Type

Main breaker

### Amperage Rating

150 A

### Bus material

Copper

### Main circuit breaker

CSR

### Number of circuits

24

### Number of spaces

24

### Phase

Single-phase

### Wire size

#2/0 AWG-300 kcmil

### Feed type

Overhead

### Voltage rating

120/240 V

### Box size

E

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CH24B150R](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)