



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CH 3/4-inch loadcenter

CH24L225D

UPC:782113097732

### Dimensions:

- **Height:** 5.19 IN
- **Length:** 21 IN
- **Width:** 14.31 IN

**Notes:** Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

### Warranties:

- Limited lifetime

### Specifications:

- **Special Features:** Standard
- **Type:** Main lug only
- **Amperage Rating:** 225A
- **Box Size:** D
- **Bus Material:** Copper
- **Cover:** Ch8df-combination, ch8ds-surface
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Feed Type:** Overhead or underground
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 24
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #4-300 kcmil

### Supporting documents:

- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - CH24L225D](#)



- Dimensional Drawing - CH 3/4 LOADCENTER,  
MAIN LUG ONLY, INDOOR NEMA 1, 120/240  
VAC, 1 PHASE

**Certifications:**

- UL 50
- UL 67

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CH 3/4-inch loadcenter

CH24L225D

UPC:782113097732

### Dimensions:

- **Height:** 5.19 IN
- **Length:** 21 IN
- **Width:** 14.31 IN

**Notes:** Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

### Warranties:

- Limited lifetime

### Specifications:

- **Special Features:** Standard
- **Type:** Main lug only
- **Amperage Rating:** 225A
- **Box Size:** D
- **Bus Material:** Copper
- **Cover:** Ch8df-combination, ch8ds-surface
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Feed Type:** Overhead or underground
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 24
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #4-300 kcmil

### Supporting documents:

- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - CH24L225D](#)



- Dimensional Drawing - CH 3/4 LOADCENTER,  
MAIN LUG ONLY, INDOOR NEMA 1, 120/240  
VAC, 1 PHASE

**Certifications:**

- UL 50
- UL 67

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.