

Eaton CH32BPN200J

Catalog Number: CH32BPN200J

CH 3/4-inch loadcenter, Plug-on neutral, Main breaker, 200A, J, Copper, Ch8jf-combination, ch8js-surface, not included, NEMA 1, Metallic, 35 kAIC, CSH, 32, 32, Three-wire, Single-phase, #2/0 AWG-300 kcmil



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CH32BPN200J
UPC	Product Length/Depth
782116983377	34.13 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
15.8 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Single phase convertible loadcenters with main breaker included

Product specifications

Special features

Plug-on neutral

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Cover

Ch8jf-combination, ch8js-surface, not included

Main circuit breaker

CSH

Number of circuits

32

Number of spaces

32

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil

Box size

J

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

35 kAIC

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH32BPN200J](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CH32BPN200J

Catalog Number: CH32BPN200J

CH 3/4-inch loadcenter, Plug-on neutral, Main breaker, 200A, J, Copper, Ch8jf-combination, ch8js-surface, not included, NEMA 1, Metallic, 35 kAIC, CSH, 32, 32, Three-wire, Single-phase, #2/0 AWG-300 kcmil



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CH32BPN200J
UPC	Product Length/Depth
782116983377	34.13 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
15.8 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Single phase convertible loadcenters with main breaker included

Product specifications

Special features

Plug-on neutral

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Cover

Ch8jf-combination, ch8js-surface, not included

Main circuit breaker

CSH

Number of circuits

32

Number of spaces

32

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil

Box size

J

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

35 kAIC

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH32BPN200J](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)