



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CH 3/4-inch main loadcenter

CH42B200K

UPC:782113098210

### Dimensions:

- **Height:** 3.88 IN
- **Length:** 37 IN
- **Width:** 14.31 IN

**Notes:** Loadcenter can be overhead or underground fed by rotating the enclosure and trim 180 degrees.

### Warranties:

- Limited lifetime

### Specifications:

- **Special Features:** Standard
- **Type:** Main breaker
- **Amperage Rating:** 200A
- **Box Size:** K
- **Bus Material:** Copper
- **Cover:** Ch8kf-combination, ch8ks-surface
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** CSR
- **Number Of Circuits:** 42
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2 AWG-300 kcmil
- **Feed Type:** Top/bottom

### Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CSR MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters -](#)



## Instructions

- [Eaton Specification Sheet - CH42B200K](#)

## Certifications:

- UL 67
- UL 50

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CH 3/4-inch main loadcenter

CH42B200K

UPC:782113098210

### Dimensions:

- **Height:** 3.88 IN
- **Length:** 37 IN
- **Width:** 14.31 IN

**Notes:** Loadcenter can be overhead or underground fed by rotating the enclosure and trim 180 degrees.

### Warranties:

- Limited lifetime

### Specifications:

- **Special Features:** Standard
- **Type:** Main breaker
- **Amperage Rating:** 200A
- **Box Size:** K
- **Bus Material:** Copper
- **Cover:** Ch8kf-combination, ch8ks-surface
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** CSR
- **Number Of Circuits:** 42
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2 AWG-300 kcmil
- **Feed Type:** Top/bottom

### Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CSR MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters -](#)



## Instructions

- [Eaton Specification Sheet - CH42B200K](#)

## **Certifications:**

- UL 67
- UL 50

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.