

Eaton CH42L225R

Catalog Number: CH42L225R

Eaton CH main lug loadcenters, Standard, Main lug only, 225A, G, Copper, NEMA 3R, Metallic, Overhead, CH, 42, 42, Three-wire, Single-phase, 120/240 V, #4 AWG-300 kcmil



Photo is representative

General specifications

Product Name

Eaton CH main lug loadcenter

Catalog Number

CH42L225R

UPC

782113098357

Product Length/Depth

34.13 in

Product Height

5.19 in

Product Width

14.31 in

Product Weight

15 lb

Warranty

Limited lifetime

Certifications

UL 50

UL 67

Catalog Notes

Rainproof panels are furnished with hub closure plates. Suitable for use as a service equipment when a circuit breaker is used as a main breaker. The main breaker is backfed and requires hold-down bracket kit catalog number ch125rb.



Powering Business Worldwide

Product specifications

Special features

Standard

Type

Main lug only

Amperage Rating

225 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

42

Number of spaces

42

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#4 AWG-300 kcmil

Box size

G

Enclosure

NEMA 3R

Enclosure material

Metallic

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH42L225R](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)