



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 1P/CH 60 SPACE/120 CKTS 225A MLO INDOOR PLUG-ON NEUTRAL

CH60NLPN225N

UPC:786685931821

### Dimensions:

- **Height:** 43.4 IN
- **Length:** 3.9 IN
- **Width:** 14.3 IN

**Weight:**32 LB

**Warranties:** No Data

### Specifications:

- **Special Features:** Plug-on neutral
- **Type:** Convertible
- **Amperage Rating:** 225A
- **Bus Material:** Copper
- **Enclosure:** NEMA 1
- **Number Of Circuits:** 120
- **Number Of Spaces:** 60
- **Phase:** Single-phase
- **Feed Type:** Top or bottom feed
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - CH60NLPN225N](#)

**Certifications:** No Data

### Product compliance:

- UL67





Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 1P/CH 60 SPACE/120 CKTS 225A MLO INDOOR PLUG-ON NEUTRAL

CH60NLPN225N

UPC:786685931821

### Dimensions:

- **Height:** 43.4 IN
- **Length:** 3.9 IN
- **Width:** 14.3 IN

**Weight:**32 LB

**Warranties:** No Data

### Specifications:

- **Special Features:** Plug-on neutral
- **Type:** Convertible
- **Amperage Rating:** 225A
- **Bus Material:** Copper
- **Enclosure:** NEMA 1
- **Number Of Circuits:** 120
- **Number Of Spaces:** 60
- **Phase:** Single-phase
- **Feed Type:** Top or bottom feed
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - CH60NLPN225N](#)

**Certifications:** No Data

### Product compliance:

- UL67

