

# Eaton CHEC24L125E

Catalog Number: CHEC24L125E

Eaton CH surge loadcenter, Provision only, Convertible, 125 A, E, 24 Circuits, #6-4/0 AWG

## General specifications



Photo is representative

<b>Product Name</b>	Eaton CH surge loadcenter	<b>Catalog Number</b>	CHEC24L125E
<b>UPC</b>	782116200146	<b>Product Length/Depth</b>	32 in
<b>Product Height</b>	3 in	<b>Product Width</b>	10 in
<b>Product Weight</b>	7 lb	<b>Warranty</b>	Limited lifetime
<b>Certifications</b>	UL Listed	<b>Catalog Notes</b>	Order Cover CHSUR8ES or CHSUR8EF separately. CHSPT2ULTRA and breaker not included

## Product specifications

### Special features

Provision only

### Type

Main lug only

### Amperage Rating

125 A

### Bus material

Aluminum

### Number of circuits

32

### Number of spaces

32

### Phase

Single-phase

### Wire size

#6-4/0 AWG

### Box size

E

### Enclosure

NEMA 1

### Interrupt rating

25 kAIC

## Resources

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHEC24L125E](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CHEC24L125E

Catalog Number: CHEC24L125E

Eaton CH surge loadcenter, Provision only, Convertible, 125 A, E, 24 Circuits, #6-4/0 AWG

## General specifications



Photo is representative

**Product Name**  
Eaton CH surge loadcenter

**Catalog Number**  
CHEC24L125E

**UPC**  
782116200146

**Product Length/Depth**  
32 in

**Product Height**  
3 in

**Product Width**  
10 in

**Product Weight**  
7 lb

**Warranty**  
Limited lifetime

**Certifications**  
UL Listed

**Catalog Notes**  
Order Cover CHSUR8ES or CHSUR8EF separately. CHSPT2ULTRA and breaker not included

## Product specifications

### Special features

Provision only

### Type

Main lug only

### Amperage Rating

125 A

### Bus material

Aluminum

### Number of circuits

32

### Number of spaces

32

### Phase

Single-phase

### Wire size

#6-4/0 AWG

### Box size

E

### Enclosure

NEMA 1

### Interrupt rating

25 kAIC

## Resources

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHEC24L125E](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)