

Specifications

Photo is representative



Eaton CHEC24L125E

Eaton CH surge loadcenter, Provision only, Convertible, 125 A, E, 24 Circuits, #6-4/0 AWG

Product specifications

SPECIAL FEATURES	Provision only
TYPE	Main lug only
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
NUMBER OF CIRCUITS	32
NUMBER OF SPACES	32
PHASE	Single-phase
WIRE SIZE	#6-4/0 AWG
BOX SIZE	E
ENCLOSURE	NEMA 1
INTERRUPT RATING	25 kAIC

General specifications

PRODUCT NAME	Eaton CH surge loadcenter
CATALOG NUMBER	CHEC24L125E
UPC	782116200146
PRODUCT LENGTH/DEPTH	32 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	7 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL Listed
CATALOG NOTES	Order Cover CHSUR8ES or CHSUR8EF separately. CHSPT2ULTRA and breaker not included

Powering Business Worldwide

Specifications

Photo is representative



Eaton CHEC24L125E

Eaton CH surge loadcenter, Provision only, Convertible, 125 A, E, 24 Circuits, #6-4/0 AWG

Product specifications

SPECIAL FEATURES	Provision only
TYPE	Main lug only
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
NUMBER OF CIRCUITS	32
NUMBER OF SPACES	32
PHASE	Single-phase
WIRE SIZE	#6-4/0 AWG
BOX SIZE	E
ENCLOSURE	NEMA 1
INTERRUPT RATING	25 kAIC

General specifications

PRODUCT NAME	Eaton CH surge loadcenter
CATALOG NUMBER	CHEC24L125E
UPC	782116200146
PRODUCT LENGTH/DEPTH	32 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	7 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL Listed
CATALOG NOTES	Order Cover CHSUR8ES or CHSUR8EF separately. CHSPT2ULTRA and breaker not included



Powering Business Worldwide