

# Eaton CHEC32N225KRNSP

Catalog Number: CHEC32N225KRNSP

Eaton CH surge loadcenter, Includes renovation terminal blocks, Type CH surge ready loadcenter, 225 A, 32 Circuits



## General specifications

Product Name	Eaton CH surge loadcenter	Catalog Number	CHEC32N225KRNSP
UPC	782116984183	Product Length/Depth	37.5 in
Product Height	4 in	Product Width	15 in
Product Weight	22 lb	Warranty	Limited lifetime
Certifications	UL Listed	Catalog Notes	Order Cover CHSUR8KS or CHSUR8KF separately

## Product specifications

### Special features

Includes renovation terminal blocks

### Type

Surge loadcenter

### Amperage Rating

225 A

### Bus material

Aluminum

### Number of circuits

32

### Number of spaces

32

### Phase

Single-phase

### Enclosure

NEMA 1

### Interrupt rating

25 kAIC

## Resources

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHEC32N225KRNSP](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CHEC32N225KRNSP

Catalog Number: CHEC32N225KRNSP

Eaton CH surge loadcenter, Includes renovation terminal blocks, Type CH surge ready loadcenter, 225 A, 32 Circuits



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH surge loadcenter	CHEC32N225KRNSP
<b>UPC</b>	<b>Product Length/Depth</b>
782116984183	37.5 in
<b>Product Height</b>	<b>Product Width</b>
4 in	15 in
<b>Product Weight</b>	<b>Warranty</b>
22 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed	Order Cover CHSUR8KS or CHSUR8KF separately

## Product specifications

### Special features

Includes renovation terminal blocks

### Type

Surge loadcenter

### Amperage Rating

225 A

### Bus material

Aluminum

### Number of circuits

32

### Number of spaces

32

### Phase

Single-phase

### Enclosure

NEMA 1

### Interrupt rating

25 kAIC

## Resources

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHEC32N225KRNSP](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)