



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHF220SW 2P 20A 240V TF Switching Neutral Breaker

Eaton Corp

Catalog Number	CHF220SW
Manufacturer	Eaton Corp
Description	Switching Neutral Breaker, 20 A, Common Tripping Mechanism, Line and Load Lug Terminal, Plug-In, 120/240 V Ac, 0.42 In Overall Height, 1.5 In Overall Length, 5 In Overall Width
Weight per unit	1.0 (lbs/each)
Product Category	2P Special Application Plug-In

Features

amperage rating	20
class	1.0000 IN X 1.0000 IN X 2.2300 IN
Contact Configuration	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
Cord Type	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
element	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
Poles	2
Trip Type	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
used with	Type CH Loadcenters
Wire Size	#14-8 AWG Cu/Al

Material, Color, and Finish

Style	Open Office, Retail
-------	---------------------

Dimensions and Weight

Height	3.5
Length	1.5
Width	5

Descriptions

Description	2P 20A 240V TF SWITCHING NEUTRAL BREAKER
extra long description	ETN CH220SW

Manufacturer Information

GTIN	00782113101781
series	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
sub brand	Open Office, Retail
UPC	782113101781



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Specialty Breakers (Quad, Dupl, Shunt Trip)

Availability

Manufacturer Status Inactive

Packaging

Carton 1

Weight Per each 1

Uses, Certifications, and Standards

standard UL 489