

# Eaton CHM1N7N7NSU

Catalog Number: CHM1N7N7NSU

Eaton pedestal mount metered, Metered-ring, 50A, Non-ground fault, Non-ground fault, Non-ground fault, Bottom, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 14-50R, NEMA 5-20R2GFI, 250V



Photo is representative

## General specifications

### Product Name

Eaton pedestal mount metered

### Catalog Number

CHM1N7N7NSU

### UPC

786685404264

### Product Length/Depth

7.25 in

### Product Height

31 in

### Product Width

10 in

### Product Weight

30 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed file E163588

UL 231

## Physical Attributes

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

Non-ground fault

### Feed type

Bottom

### Mounting

Surface

### Number of circuits

4

### Receptacle center

NEMA 5-20R2GFI

### Receptacle left

NEMA 14-50R

### Receptacle right

NEMA 5-20R2GFI

### Type

Metered-ring

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHM1N7N7NSU](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)