



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHN230SUR Surge Breaker, 2P, 30A, 120/240V, 10kaic *Eaton Corp*

Catalog Number	CHN230SUR
Manufacturer	Eaton Corp
Description	Eaton CH Residential Surge Breaker, 2P, 30A, 120/240V, 10KAIC, Pigtail Neutral
Weight per unit	0.6000 (lbs/each)
Product Category	2 Pole

Features

amperage rating	30
-----------------	----

Dimensions and Weight

Height	2.25
Length	3.5
Width	6

Descriptions

Description	SURGE BREAKER, 2P, 30A, 120/240V, 10KAIC
extra long description	ETN CHN230SUR Surge Breaker, 2P, 30
Features	Eaton offers a comprehensive family of surge products for use at service entrances. These products can help protect sensitive electronics against the damaging effects of surges. Due to the evolution of electronics and microprocessors in the home, there is a continuous challenge to provide quality (clean) power for electronic loads such as appliances, computers/home office and entertainment systems. Surges caused by lightning, utility grid switching and other sources travel on current carrying conductors t
Long Description	Eaton CH residential surge breaker, 2P, 30A, 120/240V, 10KAIC, PIGTAIL NEUTRAL
Product Type	Surge Breaker, 2P, 30A, 120/240V, 10kaic

Manufacturer Information

Brand	Eaton
GTIN	00786689217174
Manufacturers Part Number	CHN230SUR
UPC	786689217174

Taxonomies, Classifications, and Categories

Type	Surge breaker
------	---------------

Packaging

Carton	1
Weight Per each	0.6



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Conventional Energy - Conventional
EnergyOtherDatacenters - IT Space: CI and Hyper
ConvergedMarine Vessels and Equipment - Marine Vessels and
Equipment - OtherGeneration - Renewable Energy - Alternative
Energy

standard

UL 489,UL 1449