

Eaton CHP24B150X5

Catalog Number: CHP24B150X5

Eaton CH main breaker loadcenters, PON, Main breaker, 150 A, X5, Copper, X5, NEMA 1, Metallic, 10 kAIC, CSR, 48, 24, Three-wire, Single-phase, #2 AWG-300 kcmil, 120/240 V



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP24B150X5
UPC	Product Length/Depth
786679189573	29 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
17.5 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Purchase Size X5 Cover Separately

Product specifications

Special features

PON

Type

Main breaker

Amperage Rating

150 A

Bus material

Copper

Cover

X5

Main circuit breaker

CSR

Number of circuits

48

Number of spaces

24

Phase

Single-phase

Wire size

#2 AWG-300 kcmil

Voltage rating

120/240 V

Box size

X5

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP24B150X5](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)