



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHP24L225X5 CH Pon Loadcnr 225A Mlo 24 Spaces

Eaton Corp

Catalog Number	CHP24L225X5
Manufacturer	Eaton Corp
Description	Eaton CH Main Lug Loadcenters, Pon, CH, 225A, X5, Copper, !, Nema 1 Indoor, Steel, 25 Kaic, 48, 24, 3, Single-Phase, 120/240 V, #4 Awg-300 Kcmil
Weight per unit	16.4 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	225
interrupt rating	25
media	Yes
number of spaces	24
Phase	1
Voltage Rating	120/240 V

Dimensions and Weight

Depth	29
Height	4
Size	X5
Width	14.3

Descriptions

Description	CH PON LOADCNR 225A MLO 24 SPACES
extra long description	ETN CHP24L225X5 CH PON Loadcenter,
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main lug loadcenters,PON,CH,225A,X5,Copper,!,NEMA 1 indoor,Steel,25 kAIC,48,24,3,Single-phase,120/240 V,#4 AWG-300 kcmil
Product Type	CH Pon Loadcenter, 225A, Mlo, 24 Spaces
Special Features	PON



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00786689054281
Manufacturers Part Number	CHP24L225X5
UPC	786689054281

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main lug loadcenter

Packaging

Carton	1
Weight Per each	16.4

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL 67