

# Eaton CHP42L225

Catalog Number: CHP42L225

Eaton CH main lug loadcenters, PON, Main Lug Only, 225A, X6, Copper, Cover included, NEMA 1 indoor, Metallic, 10 kAIC, 84, Single-pole, 42, Two hots, a neutral and a ground, Single-phase, 120/240 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main lug loadcenter	CHP42L225
<b>UPC</b>	<b>Product Length/Depth</b>
786689054618	35.8 in
<b>Product Height</b>	<b>Product Width</b>
5 in	15.9 in
<b>Product Weight</b>	<b>Warranty</b>
31.25 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67	Retail Packaging
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

Main Lug Only

### Amperage Rating

225 A

### Bus material

Copper

### Cover

Cover included

### Number of circuits

84

### Number Of Poles

Single-pole

### Number of spaces

42

### Phase

Single-phase

### Voltage rating

120/240 V

### Wire size

#1 AWG-300 kcmil

### Box size

X6

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

Two hots, neutral and ground

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP42L225](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton CHP42L225

Catalog Number: CHP42L225

Eaton CH main lug loadcenters,PON,Main Lug Only,225A,X6,Copper,Cover included,NEMA 1 indoor,Metallic,10 kAIC,84,Single-pole,42,Two hots, a neutral and a ground,Single-phase,120/240 V



## General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CHP42L225
UPC	Product Length/Depth
786689054618	35.8 in
Product Height	Product Width
5 in	15.9 in
Product Weight	Warranty
31.25 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Retail Packaging
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

Main Lug Only

### Amperage Rating

225 A

### Bus material

Copper

### Cover

Cover included

### Number of circuits

84

### Number Of Poles

Single-pole

### Number of spaces

42

### Phase

Single-phase

### Voltage rating

120/240 V

### Wire size

#1 AWG-300 kcmil

### Box size

X6

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

Two hots, neutral and ground

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP42L225](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)