

Eaton CHP60B200X9

Catalog Number: CHP60B200X9

Eaton CH main breaker loadcenters, PON, Main breaker, 200 A, X9, Copper, X9, NEMA 1, Metallic, 25 kAIC, CSR, 120, 60, Three-wire, Single-phase, #2 AWG-300 kcmil, 120/240 V



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP60B200X9
UPC	Product Length/Depth
786679189665	45 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
27 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Purchase Size X9 Cover Separately

defaultTaxonomyAttributeLabel

Special features

PON

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Cover

X9

Main circuit breaker

CSR

Number of circuits

120

Number of spaces

60

Phase

Single-phase

Wire size

#2 AWG-300 kcmil

Voltage rating

120/240 V

Box size

X9

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CHP60B200X9

Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia