

Eaton CHR7N7NS

Catalog Number: CHR7N7NS

Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Top, Surface, Circuits: 4, Center: NEMA 5-20R2GFI, Left: NEMA 5-20R2GFI, Right: None, Ringless



General specifications

Product Name

Eaton pedestal mount metered

Catalog Number

CHR7N7NS

UPC

782114203293

Product Length/Depth

31 in

Product Height

8 in

Product Width

10 in

Product Weight

24 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed file E163588

UL 231

Product specifications

Type

Metered-ringless

Utility approvals

IA : Alliant (IP&L and WP&L)

WI : Alliant (IP&L and WP&L)

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

FL : Tallahassee City Electric

Circuit breaker position 1

Ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

None

Receptacle center

NEMA 5-20R2GFI

Receptacle left

NEMA 5-20R2GFI

Receptacle right

None

Feed type

Top

Mounting

Surface

Number of circuits

4

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHR7N7NS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)