



Powering Business Worldwide

pe.eaton.com

SPD Type 2 CHSP Service Entrance Surge Protection

CHSPT2SURGE

UPC:786685971285

Dimensions:

- **Height:** 2 IN
- **Length:** 7.5 IN
- **Width:** 5 IN

Weight:.85 LB

Notes:5kA nominal discharge current. Has 36kA one time surge current rating.

Warranties:

- Limited lifetime

Specifications:

- **Frequency Rating:** 60 Hz
- **Nominal Discharge Current:** 5000 KA
- **Operating Voltage:** 150V L-N, 300V L-L
- **Protection:** 700V L-N, 1200V L-L, 900V N-G, 700V L-G
- **Short Circuit Rating:** 22000 KA
- **Voltage Rating:** 120/240V
- **Enclosure:** NEMA 4
- **Phase:** Single-phase
- **Surge Current:** 36 kA

Supporting documents:

- [Eaton Specification Sheet - CHSPT2SURGE](#)

Certifications: No Data

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

SPD Type 2 CHSP Service Entrance Surge Protection

CHSPT2SURGE

UPC:786685971285

Dimensions:

- **Height:** 2 IN
- **Length:** 7.5 IN
- **Width:** 5 IN

Weight:.85 LB

Notes:5kA nominal discharge current. Has 36kA one time surge current rating.

Warranties:

- Limited lifetime

Specifications:

- **Frequency Rating:** 60 Hz
- **Nominal Discharge Current:** 5000 KA
- **Operating Voltage:** 150V L-N, 300V L-L
- **Protection:** 700V L-N, 1200V L-L, 900V N-G, 700V L-G
- **Short Circuit Rating:** 22000 KA
- **Voltage Rating:** 120/240V
- **Enclosure:** NEMA 4
- **Phase:** Single-phase
- **Surge Current:** 36 kA

Supporting documents:

- [Eaton Specification Sheet - CHSPT2SURGE](#)

Certifications: No Data

Product compliance: No Data

