

## Eaton pedestal mount unmetered

**CHU1N9N4NPTZ**

**UPC:**786680206795

### **Dimensions:**

- **Height:** 39.9 IN
- **Length:** 6.8 IN
- **Width:** 9.5 IN

**Weight:**45 LB

### **Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### **Specifications:**

- **Special Features:** Factory installed pedestal extension with lay-in ground lug
- **Type:** Unmetered
- **Circuit Breaker Position 1:** Non-ground fault
- **Feed Type:** Top
- **Mounting:** Pedestal
- **Number Of Circuits:** 4
- **Receptacle Center:** NEMA 5-20R2GFI/weather and tamper resistant
- **Receptacle Left:** NEMA 14-50R
- **Receptacle Right:** NEMA TT-30R

### **Supporting documents:**

- [Eaton Specification Sheet - CHU1N9N4NPTZ](#)

### **Certifications:**

- UL 231
- UL Listed file E163588

**Product compliance:** No Data





## Eaton pedestal mount unmetered

**CHU1N9N4NPTZ**

**UPC:**786680206795

**Dimensions:**

- **Height:** 39.9 IN
- **Length:** 6.8 IN
- **Width:** 9.5 IN

**Weight:**45 LB

**Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Specifications:**

- **Special Features:** Factory installed pedestal extension with lay-in ground lug
- **Type:** Unmetered
- **Circuit Breaker Position 1:** Non-ground fault
- **Feed Type:** Top
- **Mounting:** Pedestal
- **Number Of Circuits:** 4
- **Receptacle Center:** NEMA 5-20R2GFI/weather and tamper resistant
- **Receptacle Left:** NEMA 14-50R
- **Receptacle Right:** NEMA TT-30R

**Supporting documents:**

- [Eaton Specification Sheet - CHU1N9N4NPTZ](#)

**Certifications:**

- UL 231
- UL Listed file E163588

**Product compliance:** No Data



