

# Specifications



## Eaton CHU4N7NS

Eaton pedestal mount unmetered, Unmetered, 30A, 20A, None, Non-ground fault, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA TT-30R, NEMA 5-20R2GFI, None, 3, 3, 0, 125V, 125V, None

### General specifications

<b>PRODUCT NAME</b>	Eaton pedestal mount unmetered
<b>CATALOG NUMBER</b>	CHU4N7NS
<b>UPC</b>	782114203743
<b>PRODUCT LENGTH/DEPTH</b>	13.6 in
<b>PRODUCT HEIGHT</b>	39.9 in
<b>PRODUCT WIDTH</b>	9.5 in
<b>PRODUCT WEIGHT</b>	8.6 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed file E163588 UL 231

## Physical Attributes

<b>CIRCUIT BREAKER POSITION 1</b>	Non-ground fault
-----------------------------------	------------------

<b>CIRCUIT BREAKER POSITION 2</b>	Non-ground fault
-----------------------------------	------------------

<b>CIRCUIT BREAKER POSITION 3</b>	None
-----------------------------------	------

<b>FEED TYPE</b>	Top
------------------	-----

<b>MOUNTING</b>	Surface
-----------------	---------

<b>NUMBER OF CIRCUITS</b>	4
---------------------------	---

<b>RECEPTACLE CENTER</b>	NEMA 5-20R2GFI
--------------------------	----------------

<b>RECEPTACLE LEFT</b>	NEMA TT-30R
------------------------	-------------

<b>RECEPTACLE RIGHT</b>	None
-------------------------	------

<b>TYPE</b>	Unmetered
-------------	-----------

## Resources

### CATALOGS

[Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CHU4N7NS](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications



## Eaton CHU4N7NS

Eaton pedestal mount unmetered, Unmetered, 30A, 20A, None, Non-ground fault, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA TT-30R, NEMA 5-20R2GFI, None, 3, 3, 0, 125V, 125V, None

### General specifications

<b>PRODUCT NAME</b>	Eaton pedestal mount unmetered
<b>CATALOG NUMBER</b>	CHU4N7NS
<b>UPC</b>	782114203743
<b>PRODUCT LENGTH/DEPTH</b>	13.6 in
<b>PRODUCT HEIGHT</b>	39.9 in
<b>PRODUCT WIDTH</b>	9.5 in
<b>PRODUCT WEIGHT</b>	8.6 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed file E163588 UL 231

## Physical Attributes

<b>CIRCUIT BREAKER POSITION 1</b>	Non-ground fault
-----------------------------------	------------------

<b>CIRCUIT BREAKER POSITION 2</b>	Non-ground fault
-----------------------------------	------------------

<b>CIRCUIT BREAKER POSITION 3</b>	None
-----------------------------------	------

<b>FEED TYPE</b>	Top
------------------	-----

<b>MOUNTING</b>	Surface
-----------------	---------

<b>NUMBER OF CIRCUITS</b>	4
---------------------------	---

<b>RECEPTACLE CENTER</b>	NEMA 5-20R2GFI
--------------------------	----------------

<b>RECEPTACLE LEFT</b>	NEMA TT-30R
------------------------	-------------

<b>RECEPTACLE RIGHT</b>	None
-------------------------	------

<b>TYPE</b>	Unmetered
-------------	-----------

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5</a>
-----------------	---

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHU4N7NS</a>
--------------------------------------	--

<b>PROJECT NAME:</b>
----------------------

<b>PROJECT NUMBER:</b>
------------------------

<b>PREPARED BY:</b>
---------------------

<b>DATE:</b>
--------------



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.