

# Specifications

## Eaton CHU4N7NS

Eaton pedestal mount unmetered, Unmetered, 30A, 20A, None, Non-ground fault, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA TT-30R, NEMA 5-20R2GFI, None, 3, 3, 0, 125V, 125V, None



### General specifications

<b>PRODUCT NAME</b>	Eaton pedestal mount unmetered
<b>CATALOG NUMBER</b>	CHU4N7NS
<b>UPC</b>	782114203743
<b>PRODUCT LENGTH/DEPTH</b>	13.6 in
<b>PRODUCT HEIGHT</b>	39.9 in
<b>PRODUCT WIDTH</b>	9.5 in
<b>PRODUCT WEIGHT</b>	8.6 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed file E163588 UL 231

### Product specifications

<b>TYPE</b>	Unmetered
<b>CIRCUIT BREAKER POSITION 1</b>	Non-ground fault
<b>CIRCUIT BREAKER POSITION 2</b>	Non-ground fault
<b>CIRCUIT BREAKER POSITION 3</b>	None
<b>RECEPTACLE CENTER</b>	NEMA 5-20R2GFI
<b>RECEPTACLE LEFT</b>	NEMA TT-30R
<b>RECEPTACLE RIGHT</b>	None
<b>FEED TYPE</b>	Top
<b>MOUNTING</b>	Surface
<b>NUMBER OF CIRCUITS</b>	4

### Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHU4N7NS</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton CHU4N7NS

Eaton pedestal mount unmetered, Unmetered, 30A, 20A, None, Non-ground fault, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA TT-30R, NEMA 5-20R2GFI, None, 3, 3, 0, 125V, 125V, None



### General specifications

<b>PRODUCT NAME</b>	Eaton pedestal mount unmetered
<b>CATALOG NUMBER</b>	CHU4N7NS
<b>UPC</b>	782114203743
<b>PRODUCT LENGTH/DEPTH</b>	13.6 in
<b>PRODUCT HEIGHT</b>	39.9 in
<b>PRODUCT WIDTH</b>	9.5 in
<b>PRODUCT WEIGHT</b>	8.6 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed file E163588 UL 231

### Product specifications

<b>TYPE</b>	Unmetered
<b>CIRCUIT BREAKER POSITION 1</b>	Non-ground fault
<b>CIRCUIT BREAKER POSITION 2</b>	Non-ground fault
<b>CIRCUIT BREAKER POSITION 3</b>	None
<b>RECEPTACLE CENTER</b>	NEMA 5-20R2GFI
<b>RECEPTACLE LEFT</b>	NEMA TT-30R
<b>RECEPTACLE RIGHT</b>	None
<b>FEED TYPE</b>	Top
<b>MOUNTING</b>	Surface
<b>NUMBER OF CIRCUITS</b>	4

### Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHU4N7NS</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

