

# Eaton CHU4N7NS

Catalog Number: CHU4N7NS

Eaton pedestal mount unmetered, Unmetered, 30A, 20A, None, Non-ground fault, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA TT-30R, NEMA 5-20R2GFI, None, 3, 3, 0, 125V, 125V, None

## General specifications



### Product Name

Eaton pedestal mount unmetered

### Catalog Number

CHU4N7NS

### UPC

782114203743

### Product Length/Depth

13.6 in

### Product Height

39.9 in

### Product Width

9.5 in

### Product Weight

8.6 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed file E163588

UL 231

## Product specifications

### Type

Unmetered

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

None

### Receptacle center

NEMA 5-20R2GFI

### Receptacle left

NEMA TT-30R

### Receptacle right

None

### Feed type

Top

### Mounting

Surface

### Number of circuits

4

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHU4N7NS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)