

# Specifications



## Eaton CHU6G6G5GS

Eaton pedestal mount unmetered, 20A, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2, NEMA 6-20R2, 3, 125V, 250V

### General specifications

<b>PRODUCT NAME</b>	Eaton pedestal mount unmetered
<b>CATALOG NUMBER</b>	CHU6G6G5GS
<b>UPC</b>	782114203927
<b>PRODUCT LENGTH/DEPTH</b>	4.3 in
<b>PRODUCT HEIGHT</b>	17.1 in
<b>PRODUCT WIDTH</b>	9.5 in
<b>PRODUCT WEIGHT</b>	16.25 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed file E163588 UL 231

## Product specifications

TYPE	Unmetered
CIRCUIT BREAKER POSITION 1	Ground fault
CIRCUIT BREAKER POSITION 2	Ground fault
CIRCUIT BREAKER POSITION 3	Ground fault
RECEPTACLE CENTER	NEMA 5-20R2
RECEPTACLE LEFT	NEMA 5-20R2
RECEPTACLE RIGHT	NEMA 6-20R2
FEED TYPE	Top
MOUNTING	Surface
NUMBER OF CIRCUITS	4

## Resources

### CATALOGS

[Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CHU6G6G5GS](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

