

Eaton CHU7N7N5NS

Catalog Number: CHU7N7N5NS

Eaton pedestal mount unmetered, 20A, Non-ground fault, Top, Surface, Circ: 4, NEMA 6-20R2, 3, 125V, 250V

General specifications



Product Name

Eaton pedestal mount unmetered

Catalog Number

CHU7N7N5NS

UPC

782114203941

Product Length/Depth

18.2 in

Product Height

7.9 in

Product Width

10 in

Product Weight

16 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231

UL Listed file E163588

Product specifications

Type

Unmetered

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Receptacle center

NEMA 5-20R2GFI

Receptacle left

NEMA 5-20R2GFI

Receptacle right

NEMA 6-20R2

Feed type

Top

Mounting

Surface

Number of circuits

4

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHU7N7N5NS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia