

Eaton CLGF115

Catalog Number: CLGF115

Eaton Classified 1" GFCI circuit breaker, Ground fault circuit breaker, 15 A, 10 kAIC, Single-pole, 120/240 V, CLGF, Trip-to-center, Plug-on, #14-8 AWG, Ground fault circuit interrupter, GFI

General specifications



| | |
|--|----------------------|
| Product Name | Catalog Number |
| Eaton Classified 1" GFCI circuit breaker | CLGF115 |
| UPC | Product Length/Depth |
| 786689031503 | 4 in |
| Product Height | Product Width |
| 1 in | 3.5 in |
| Product Weight | Certifications |
| 0.45 lb | Contact Manufacturer |

defaultTaxonomyAttributeLabel

Type

Ground fault circuit breaker

Amperage Rating

15 A

Voltage rating

120/240 V

Trip Type

Trip-to-center

Circuit protection

Ground fault circuit interrupter

Indicators

GFI

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

CLGF

Connection

Plug-on

Wire size

#14-8 AWG

Number of poles

Single-pole

Trip rating

15 A

Resources

Brochures

Loadcenters and Circuit Breakers

Standard circuit breaker catalog numbers - 5651B63SH09

Specifications and datasheets

Eaton Specification Sheet - CLGF115



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)