



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CMH70TU830G12 70W MH LMP

Ge By Current Lamps

Catalog Number	CMH70TU830G12
Manufacturer	Ge By Current Lamps
Description	Ge Constantcolor®, 70 WTT, 6200 LM, 3000 KV, 83 Cri, Bi-Pin (G12) Base, 15000 HR Average Life
Weight per unit	0.5800 (lbs/each)
Product Category	Hid Ceramic Metal Halide Lamps

Features

average life	15000
Base	Bi-Pin (G12)
lumens	6200
Wattage	70

Material, Color, and Finish

Color	Clear
color rendering index (cri)	83
color temperature	3000
Finish	Clear
Style	Enclosed fixtures only

Descriptions

Description	70W MH LMP
extra long description	GEL CMH70TU/830/G12 20016 MULTIVAPO
Long Description	GE ConstantColor®, 70 WTT, 6200 LM, 3000 KV, 83 CRI, Bi-Pin (G12) Base, 15000 HR Average Life
Product Type	20016 Multivapor
Special Features	3.93IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168200165
Manufacturers Part Number	CMH70TU/830/G12
UPC	043168200165

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	12
Weight Per each	0.58

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------