



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CMH70TU830G12 70W MH LMP

Ge By Current Lamps

| | |
|------------------|---|
| Catalog Number | CMH70TU830G12 |
| Manufacturer | Ge By Current Lamps |
| Description | Ge Constantcolor®, 70 WTT, 6200 LM, 3000 KV, 83 Cri, Bi-Pin (G12) Base, 15000 HR Average Life |
| Weight per unit | 0.5800 (lbs/each) |
| Product Category | Hid Ceramic Metal Halide Lamps |

Features

| | |
|--------------|--------------|
| average life | 15000.0 |
| Base | Bi-Pin (G12) |
| lumens | 6200.0 |
| Wattage | 70.0 |

Material, Color, and Finish

| | |
|-----------------------------|------------------------|
| Color | Clear |
| color rendering index (cri) | 83.0 |
| color temperature | 3000.0 |
| Finish | Clear |
| Style | Enclosed fixtures only |

Descriptions

| | |
|------------------------|---|
| Description | 70W MH LMP |
| extra long description | GEL CMH70TU/830/G12 20016 MULTIVAPO |
| Long Description | GE ConstantColor®, 70 WTT, 6200 LM, 3000 KV, 83 CRI, Bi-Pin (G12) Base, 15000 HR Average Life |
| Product Type | 20016 Multivapor |
| Special Features | 3.93IN Length |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168200165 |
| Manufacturers Part Number | CMH70TU/830/G12 |
| UPC | 043168200165 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------|
| Category Description | METAL HALIDE |
|----------------------|--------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.58 |

Uses, Certifications, and Standards

| | |
|-------------|----------------------------|
| Application | Universal burning position |
|-------------|----------------------------|