



MILBANK
ENERGY AT WORK

CP3B11115A22



Catalog Number	CP3B11115A22	Insulation	No Insulation
Marketing Product Description	Ring Type 100 Amperes 240 Volt 4 Terminal Main Circuit-breaker 16 Circuit Loadcenter 22k Mint Green	Mounting	Pad Mount
UPC	784572269699	Enclosure	G90 Galvanized Steel with Powder Coat Finish
Length (IN)	17	Jaw Quantity	4 Terminal
Width (IN)	16	Bypass Type	Link Bypass
Height (IN)	48	Number of Meter Positions	1 Position
Brand Name	Milbank	Equipment Ground	Ground Bar
Type	Ring Type Metered Commercial Pedestal	Hub Opening	No Hub Opening
Application	Power Distribution	Line Side Wire Range	4 AWG - 600 kcmil or Two 1/0 AWG - 250 kcmil
Standard	UL Listed;Type 3R	Number Of Receptacles	0
Voltage Rating	120/240 Volts Alternating Current		
Amperage Rating	100 Continuous Ampere		
Phase	1 Phase		
Frequency Rating	60 Hertz		
Size	17L x 16W x 48H		
Number Of Cutouts	1		
Cutout Size	One 100 Ampere Main Breaker		
Cable Entry	Underground		
Terminal	Single Mechanical		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.