

# 36", 42", & 48" TPI Commercial Belt Drive Portable Blowers



### Features

- Rocker switch
- SJT type cord - 3 conductor - 8' long
- Aluminum blade
- Spiral wire front and rear guards
- Powder coated 20 gauge steel housing
- 5" rubber wheels
- Meets OSHA standards / 1 Year limited warranty
- Imported to TPI specifications

### Motor Specification

- 2-Speed
- 120V
- Ball bearing
- 1-Phase
- ODP type
- Permanently lubricated

### Standard Models

MFG CATALOG NUMBER	MFG MODEL NUMBER	MOTOR HP	CFM*		VELOCITY PROFILE	MAX AMPS	WT. (LBS)
			HIGH	LOW	CFM / Area Sq Ft		
08734702	CPB 36-B	1/3	5,400	4,600	8600 / 300	4.8	82
08706602	CPB 42-B	1/2	7,600	6,700	12000 / 320	6.5	93
08722702	CPB 48-B	3/4	8,800	7,700	14000 / 500	9.0	129

\*Measured 2 feet from face of fan

Note: Photograph is a representation of stocked models. Actual model may vary in appearance.

# 24", 30", & 36" TPI Commercial Direct Drive Portable Blowers



### Features

- Rocker switch
- SJT type cord - 3 conductor - 6' long
- Spiral wire front and rear guards
- Powder coated 20 gauge steel housing
- 5" rubber wheels
- Meets OSHA standards
- 1 Year limited warranty
- Imported to TPI specifications

### Motor Specification

- 2-Speed
- 120 Volt, 1/3HP
- Ball bearing
- 1-Phase
- Open ventilated
- Permanently lubricated

### Standard Models

MFG CATALOG NUMBER	MFG MODEL NUMBER	TYPE	CFM*		VELOCITY PROFILE	MAX AMPS	CORD LENGTH	SWITCH	BLADES	WT. (LBS)
			HIGH	LOW	CFM / Area Sq Ft					
08753502	CPB 30-D	Standard / Floor	4,400	3,800	6700 / 250	3.6	6'	ROCKER	ALUMINUM	52
08710302	CPBS 30-D	Standard / Swivel	4,400	3,800	6700 / 250	3.6	6'	ROCKER	ALUMINUM	60
08722602	CPB 36-D	Standard / Floor	5,400	4,600	8500 / 300	3.6	10'	ROTARY	STEEL	70
08770102	CPBS 24-DHV	High Velocity / Swivel	3,400	2,900	5400 / 240	2.4	9'	ROTARY	ALUMINUM	38

\*Measured 2 feet from face of fan

Note: Photograph is a representation of stocked models. Actual model may vary slightly in appearance.