

Specifications

Eaton CRC3023BC



Eaton Crouse-Hinds series PowerMate CRC connector, 30A, 0.390-1.375", Two-wire, three-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CRC connector
CATALOG NUMBER	CRC3023BC
UPC	662276276482
PRODUCT LENGTH/DEPTH	6.6 in
PRODUCT HEIGHT	2.56 in
PRODUCT WIDTH	2.56 in
PRODUCT WEIGHT	2.2 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

Product specifications

AMPERAGE RATING	30A
GROUNDING TYPE	Style 2
CONFIGURATION	Two-wire, three-pole
CABLE DIAMETER	0.390-1.375"

VOLTAGE RATING

600 Vac/250 Vdc

MATERIALCopper-free aluminum

Resources

3D CAD DRAWING PACKAGE[Eaton Crouse-Hinds CRC3023BC 3D drawing](#)**BROCHURES**[PowerMate Drilling Pin and Sleeve Devices brochure](#)**CATALOGS**[PowerMate Drilling Pin and Sleeve Devices catalog page](#)**CERTIFICATION REPORTS**[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)**INSTALLATION INSTRUCTIONS**[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)**SPECIFICATIONS AND DATASHEETS**[PowerMate Connectors](#)[Eaton Specification Sheet - CRC3023BC](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton CRC3023BC



Eaton Crouse-Hinds series PowerMate CRC connector, 30A, 0.390-1.375", Two-wire, three-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CRC connector
CATALOG NUMBER	CRC3023BC
UPC	662276276482
PRODUCT LENGTH/DEPTH	6.6 in
PRODUCT HEIGHT	2.56 in
PRODUCT WIDTH	2.56 in
PRODUCT WEIGHT	2.2 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

Product specifications

AMPERAGE RATING	30A
GROUNDING TYPE	Style 2
CONFIGURATION	Two-wire, three-pole
CABLE DIAMETER	0.390-1.375"

VOLTAGE RATING

600 Vac/250 Vdc

MATERIALCopper-free aluminum

Resources

3D CAD DRAWING PACKAGE[Eaton Crouse-Hinds CRC3023BC 3D drawing](#)**BROCHURES**[PowerMate Drilling Pin and Sleeve Devices brochure](#)**CATALOGS**[PowerMate Drilling Pin and Sleeve Devices catalog page](#)**CERTIFICATION REPORTS**[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)**INSTALLATION INSTRUCTIONS**[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)**SPECIFICATIONS AND DATASHEETS**[PowerMate Connectors](#)[Eaton Specification Sheet - CRC3023BC](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

