



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS20AC1 20A 120/277VAC S Wire Comm SP SW BN

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | CS20AC1 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Toggle Switch, 1 Pole, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, Brown, Grounding Connection, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.16 LB |
| Weight per unit | 0.1640 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|-------------------|
| action | Single pole |
| amperage rating | 20 |
| Contact Rating | 20Amp, 120/277Vac |
| insulation | False |
| Poles | Single Pole |
| Switch Type | Toggle |
| Voltage | 120.0 V |

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | 20A 120/277VAC S WIRE COMM SP SW BN |
| extra long description | P&S CS20AC1 20A 120/277VAC S WIRE C |

Manufacturer Information

| | |
|-------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007126440 |
| UPC | 785007126440 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Commercial switches |
| Type | TOGGLE SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.164 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|---------------------------|
| Application | Commercial |
| Enclosure | Nylon |
| Mounting | WALL |
| standard | CULUS, FEDSPEC, UL 498/20 |