



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CS20AC3LA 20A 120/277VAC S Wire Comm 3W SW La *Pass & Seymour/Legrand*

Catalog Number	CS20AC3LA
Manufacturer	Pass & Seymour/Legrand
Description	Toggle Switch, 3 Poles, 3 Ways, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, Light Almond, Grounding Connection, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.18 LB
Weight per unit	0.1820 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Three pole
amperage rating	20
connection	Side Wire or external screw-pressure plate
Contact Configuration	One piece brass alloy contact arm
Contact Rating	Oversized silver alloy contacts
Degree of Protection	1500V Dielectric Withstand Voltage
indoor/outdoor	Indoor
insulation	False
media	Yes
Poles	3-way
Switch Type	Toggle
Voltage	120/277 V

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	20A 120/277VAC S WIRE COMM 3W SW LA
extra long description	P&S CS20AC3LA 20A 120/277VAC S WIRE

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007126549
Manufacturers Part Number	CS20AC3LA
UPC	785007126549

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage 20.0

Packaging

Carton 1

Package 50

Weight Per each 0.182

Uses, Certifications, and Standards

Application Commercial

Enclosure Nylon

Mounting WALL

standard CULUS, FEDSPEC, UL Listed E140597, Standard UL20, FedSpec
WS896, Flammability Rating UL94 V2