



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CSB20AC3BK 20A 120/277VAC B+S Wire Comm 3W SW BK

*Pass & Seymour/Legrand*

Catalog Number	CSB20AC3BK
Manufacturer	Pass & Seymour/Legrand
Description	Construction 3WAY Switch, Back and, Side Wire, 20AMP 120/277VOLT, Black.
Weight per unit	0.1893 (lbs/each)
Product Category	Gen Purpose Switches

### Features

amperage rating	20
connection	Side Wire or external screw-pressure plate
Connection Type	Wired
Contact Configuration	One piece brass alloy contact arm
Contact Rating	Oversized silver alloy contacts
Degree of Protection	1500V Dielectric Withstand Voltage
indoor/outdoor	Indoor
insulation	False
Material	Thermoplastic
Poles	3-way
Switch Type	Toggle
Voltage	120/277 V
Voltage Rating	120/277
Wattage	3

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	20A 120/277VAC B+S WIRE COMM 3W SW BK
extra long description	P&S CSB20AC3BK 20A 120/277VAC B+S W
Long Description	Construction 3way Switch, Back and, Side Wire, 20amp 120/277volt, Black.
Product Type	20A 120/277VAC B+S Wire Comm 3W SW BK
Special Features	High strength toggle, heavy duty toggle bumpers, locking support

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007108965
Manufacturers Part Number	CSB20AC3BK
UPC	785007108965



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description Residential plates  
Type SWITCH

## Trade Size

Amperage 20.0

## Packaging

Carton 1  
Package 50  
Weight Per each 0.1893

## Uses, Certifications, and Standards

Application Commercial  
Mounting WALL  
nema rating WD-1 and WD-6  
standard CULUS, FEDSPEC, UL Listed E140597, Standard UL20, FedSpec  
WS896, Flammability Rating UL94 V2