



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CSB20AC3GRY 20A 120/277VAC B+S Wire Comm 3W SW Gy

*Pass & Seymour/Legrand*

Catalog Number	CSB20AC3GRY
Manufacturer	Pass & Seymour/Legrand
Description	Construction 3WAY Switch, Back and, Side Wire, 20AMP 120/277VOLT, Gray.
Weight per unit	0.1893 (lbs/each)
Product Category	Gen Purpose Switches

### Features

amperage rating	20
connection	Side Wire or external screw-pressure plate
Connection Type	Wired
Contact Configuration	One piece brass alloy contact arm
Contact Rating	Oversized silver alloy contacts
Degree of Protection	1500V Dielectric Withstand Voltage
indoor/outdoor	Indoor
insulation	False
Material	Thermoplastic
Poles	3-way
Switch Type	Toggle
Voltage	120/277 V
Voltage Rating	120/277
Wattage	3

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	20A 120/277VAC B+S WIRE COMM 3W SW GY
extra long description	P&S CSB20AC3GRY 20A 120/277VAC B+S
Long Description	Construction 3way Switch, Back and, Side Wire, 20amp 120/277volt, Gray.
Product Type	20A 120/277VAC B+S Wire Comm 3W SW Gry
Special Features	Back & Side wire, locking support, one piece brass alloy contact arm



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007126266
Manufacturers Part Number	CSB20AC3-GRY
UPC	785007126266

## Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.1893

## Uses, Certifications, and Standards

Application	Commercial
Mounting	WALL
nema rating	WD-1 and WD-6
standard	CULUS, FEDSPEC, UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2