



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CSD201610SS 20X16X10 N4X SS4 HC QTR TRN LTCH

*Hoffman Enclosures, Inc.*

Catalog Number	CSD201610SS
Manufacturer	Hoffman Enclosures, Inc.
Description	Concept Wallmount 1/4-Turn Latch Type 4X, 20X16X10, Brushed, Stainless 304
Weight per unit	28.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### Features

ip rating	IP66
Material	Stainless Steel 304

### Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4
Style	Quarter-turn

### Dimensions and Weight

Depth	10
Height	20
Size	20.00x16.00x10.00 in
Width	16

### Descriptions

Description	20X16X10 N4X SS4 HC QTR TRN LTCH
extra long description	NVENT HOF CSD201610SS Wall Mount Ty
Features	For indoor or outdoor applications that require corrosion protection from chemicals and water. Concept Enclosures feature streamlined styling with an attractive stroked finish and flush quarter-turn latches for secure closure.
Long Description	Concept Wallmount 1/4-Turn Latch Type 4X, 20x16x10, Brushed, Stainless 304
Product Type	Wall Mount Type 4X Enclosure

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510128586
Manufacturers Part Number	CSD201610SS
UPC	783510128586

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	28

## Uses, Certifications, and Standards

Application	Corrosive Environments; Controls and Drives
nema rating	4X Watertight, corrosion-resistant